DOCUMENT: PRODUC	CT SPECIFICATIONS		DOOR APPLICATION:	BYPASSING	DRAWING SCALE:	3/4" = 1'-0" (1:16)	KROWNLAB 2351 NW York St. Portland, OR 97210
SYSTEM: FREYA			PANEL THICKNESS:	5/16" TO 1/2"	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998 KROWNL
MOUNTING STYLE: GLASS			MAXIMUM WEIGHT:	TRACK LENGTH DEPENDENT (SEE TABLE BELOW)	DATE:	3/6/2024	www.krownlab.com *DX - ORE Support@krownlab.com
DETAIL B SCALE 4"=1" (1:3)	3" MIN 3" 2"	60" 72"	MAX. PANEL WE	IGHT	4½" MAX TOTAL OVERALL SYSTEM DEF (INCLUDING FLOOR GI	GENERIC WALL SHOWN. THE TRU-LEVEL PERPENDICULAR TRACK MOUNTING DRAWING IN THE FOLLOWING PAGES COVERS SUPPORTED WALL TYPES.	support@krownlab.com SCALE: 3/8"=1' (1:32)
	17"			MOVING PANEL 2" MIN 3-1/2" MAX	Moving Panel	3 3 4	DETAIL D SCALE 4"=1' (1:3) FREYA ROLLER TRU-LEVEL TM TRACK PERPENDICULAR TRACK MOUNT

(

SECTION A-A

DETAIL C SCALE 4"=1" (1:3)

> ✓ FLOOR GUIDE* ✓ FLOOR

* = FLOOR GUIDE MAY DIFFER

EBBA FLUSH PULL SHOWN


> -DOOR STOP -SAFETY STOP


DOCUMENT:	PRODUCT SPECIFICATIONS	DOOR APPLICATION:	ALCOVE, CORNER, BYPASSING	DRAWING SCALE:	3/4" = 1'-0" (1:3)	KROWNLAB 2351 NW York St.
SYSTEM:	FREYA	PANEL THICKNESS:	5/16" TO 1/2". DOOR APPLICATION DEPENDENT	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998
MOUNTING STYLE	: GLASS	MAXIMUM WEIGHT:	DOOR APPLICATION AND TRACK CONFIGURATION DEPENDENT	DATE:	3/6/2024	www.krownlab.com support@krownlab.com



WHAT'S INCLUDED PER DOOR PANEL: 2 x - FREYA GLASS MOUNT TROLLEY KIT 1 x - FLOOR GUIDE KIT (FLOOR GUIDE MAY DIFFER - MULTIPLE OPTIONS EXIST) 1 x - TRU-LEVEL™ TRACK SYSTEM WITH ALL MOUNTING HARDWARE (SEE SEPARATE PAGE)

ALL GLASS PANELS AND FIXED MOUNTING HARDWARE MUST BE SOURCED THROUGH GLASS INSTALLER OR OTHER PARTY





OCUMENT:	PRODUCT SPECIFICATIONS - GLASS DOOR PANEL SPECIFICATIONS	DOOR APPLICATION:	ALCOVE, CORNER, BYPASSING	DRAWING SCALE:	3/4" = 1'-0" (1:12)	KROWNLAB 2351 NW York St.
YSTEM:	FREYA	PANEL THICKNESS:	5/16" TO 1/2". DOOR APPLICATION DEPENDENT	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998
OUNTING STYLE:	GLASS	MAXIMUM WEIGHT:	TRACK CONFIGURATION DEPENDENT	DATE:	1/15/2024	www.krownlab.com support@krownlab.com






ALL GLASS PANELS AND FIXED MOUNTING HARDWARE ARE TO BE SOURCED THROUGH GLASS INSTALLER OR OTHER PARTY, AND MUST MEET THE FOLLOWING REQUIREMENTS:

GLASS PANELS MUST BE FLAT POLISHED AND HAVE A 1MM CHAMFER ON ALL EDGES.

ALL HOLES MUST BE DRILLED OR CNC MACHINED WITH STRAIGHT WALLS AND SEAMED EDGES. DO NOT WATER-JET - NO TAPERED HOLES.

ALL TEMPERED GLASS IS SUBJECT TO EXPERIENCE SPONTANIOUS BREAKAGE. IT IS THE BUYERS RESPONSIBILITY TO DETERMINE AND APPROVE GLASS SPECIFICATION(S) SUITABLE TO MEET ALL FACTORS RELEVANT TO THEIR PARTICULAR USE OR APPLICATION IN CONJUNCTION WITH ALL KROWN LAB, INC.'S PRODUCTS.

REFERENCE ASTM C1048, 7.9.5



- * = 1/4" IN FORMULA ASSUMES FIXED AND RETURN PANELS STRUCTURALLY SECURED 1/8" TO 1/4" OFF FLOOR.
- ** = DISTANCE TO FLOOR TO BE DETERMINED BY INSTALLER BASED ON CHOSEN STRUCURAL FLOOR CONNECTIONS.
- *** = THE PANEL WIDTH FORMULA CREATES A 2" OVERLAP, NOT ACCOUNTING FOR NECESSARY WALL AND PANEL CLEARANCES. WIDTH PROPORTIONS ARE BASED ON NON-PROTRUDING DOOR PULLS. PROTRUDING DOOR PULLS ARE NOT COMPATIBLE WITH BYPASSING AND REQUIRE SPECIAL CONSIDERATION.

DOCUMENT:	PRODUCT SPECIFICATIONS	DOOR APPLICATION:	SINGLE & BI-PARTING	DRAWING SCALE:	6" = 1'-0" (1:2)	KROWNLAB 2351 NW York St.
SYSTEM:	TRU-LEVEL™ TRACK	PANEL THICKNESS:	3/8" TO 1/2" (CONTACT US FOR PANELS OUTSIDE OF THIS RANGE)	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998
MOUNTING STYL	E: GLASS WALL	MAXIMUM WEIGHT:	UP TO 400 LBS. TROLLEY SYSTEM OR TRACK CONFIGURATION DEPENDENT	DATE:	11/16/2023	www.krownlab.com support@krownlab.com




WHAT'S INCLUDED:

1 x TRU-LEVEL™ TRACK SYSTEM WITH ALL MOUNTING HARDWARE:


X x GLASS TRACK MOUNT KIT

2 x DOOR STOP KIT


X x TRACK CONNECTOR KIT (1 x PER TRACK JOINT INLCUDED)




* = THE DOOR STOP MAY DIFFER - MULTIPLE OPTIONS EXIST VISIT WWW.KROWNLAB.COM FOR ALL OPTIONS




TRACK SHIMS ARE DESIGNED TO BE INSTALLED AGAINST TRACK-








DOCUMENT:	PRODUCT SPECIFICATIONS - STANDARD GLASS TRACK MOUNTING POINT	DOOR APPLICATION:	SINGLE & BI-PARTING	DRAWING SCALE:	6" = 1'-0" (1:2)	KROWNLAB 2351 NW York St.
SYSTEM:	TRU-LEVEL™ TRACK	PANEL THICKNESS:	3/8" TO 1/2" (CONTACT US FOR PANELS OUTSIDE OF THIS RANGE)	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998
MOUNTING STYLE:	GLASS WALL	MAXIMUM WEIGHT:	UP TO 400 LBS. TROLLEY SYSTEM OR TRACK CONFIGURATION DEPENDENT	DATE:	11/16/2023	www.krownlab.com support@krownlab.com














CUMENT:	PRODUCT SPECIFICATIONS - PERPENDICULAR TRACK MOUNTING POINT	DOOR APPLICATION:	SINGLE, BI-PARTING, BYPASSING	DRAWING SCALE:	3/4" = 1'-0" (1:16)	KROWNLAB 2351 NW York St.
TEM:	TRU-LEVEL™ TRACK	PANEL THICKNESS:	3/8" TO 1/2" (CONTACT US FOR PANELS OUTSIDE OF THIS RANGE)	UNITS:	INCHES	Portland, OR 9/210 +1 503 292 6998 KROWNL
unting style	FRAMED WALL, TILED WALL, GLASS WALL	MAXIMUM WEIGHT:	TROLLEY SYSTEM AND TRACK CONFIGURATION DEPENDENT	DATE:	11/16/2023	www.krownlab.com support@krownlab.com
PERPENDIC SCALE: 3" =	CULAR FRAMED WALL = 1'-0" (1:4)		PERPENDICULAR TILE WALL SCALE: 3" = 1'-0" (1:4)		PERPENDICULAR GLASS WALL SCALE: 3" = 1'-0" (1:4)	
	$\begin{array}{c c} \bullet & & \\ \hline \end{array}$		1 1 8"		1 1 8"	13.n 16
↓ 3" M	1" TO $\frac{5}{8}$ " DRYWALL				SEE GLASS PANE	/32" hole EL SPECIFICATIONS — MORE DETAILS
3 M BLOCI	$2\frac{3}{16}"$ $2\frac{7}{16}"$ $2\frac{3}{8}" \text{ SLOT}$	5/8" SLOT	3" MIN BLOCKING 2\frac{1}{4}" \\ 2\frac{7}{16}" 2\frac{13}{16}" \\ 2\f	⊕	2 ¹ / ₄ "	$2\frac{7}{16}$ " $2\frac{13}{16}$ " $1\frac{7}{8}$ " HOLES
	ADJUSTABLE PERPENDICULAR TRACK MOUNT KIT FOR FRA (NOT INCLUDED) 1/4" DRYWALL INSERT DRYWALL SHIM HEIGHT ADJUSTMENT SCREW TRACK SUPPORT SOCKET SCREW PLATE PLATE SCREW END CAP SO SOCKET TRACK NUT			KET	ADJUSTABLE PERPENDICULAR TRACK (NOT INCLUDED) WASHER PLATE SCI SOCKET WASHER P GLASS BUSHING SOCKET SCREWS	REWS

DOCUMENT:	PRODUCT SPECIFICATIONS - CONFIGURATIONS	DOOR APPLICATION:	ALCOVE, CORNER, BYPASSING	DRAWING SCALE:	3/4" = 1'-0" (1:16)	KROWNLAB 2351 NW York St.	
SYSTEM:	FREYA	PANEL THICKNESS:	5/16" TO 1/2". DOOR APPLICATION DEPENDENT	UNITS:	INCHES	Portland, OR 97210 +1 503 292 6998	K
MOUNTING STYLE:	GLASS	MAXIMUM WEIGHT:	DOOR APPLICATION AND TRACK CONFIGURATION DEPENDENT	DATE:	1/15/2024	www.krownlab.com support@krownlab.com	



